### **Molex** 70543-0001 **PDF**



深圳创唯电子有限公司 http://www.molex-

connect.com

# **molex**<sup>®</sup> Test Summary

### **SL HEADER SERIES (TOLLER COMPOUNDER COMPARISON)**

#### 1.0 SCOPE

This Test Summary covers the 2.54 mm (.100 inch) centerline (pitch) printed circuit board (PCB) connector series with Tin and Gold plating.

Molex's resin manufacturer is adding an additional toller compounder. Global change notification 10659318 has been sent out detailing the change. The testing below verifies that there is no difference in the resin produced by either toller compounders.

#### 2.0 PRODUCT DESCRIPTION

#### 2.1 PRODUCT SERIES NUMBERS WITHIN SL HEADER FAMILY

#### Vertical Header Series:

70541 (Split Peg) 70543 (No Peg) 70545 (Tri-Peg) (Tested part number 70545-0024) 74099 (SMT No Peg) 74095 (Compliant Pin) 70563 (Large Pocket No Peg)

#### **Right Angle Header Series**

70551 (Split Peg) 70553 (No Peg) 70555 (Tri-Peg) 70634 (SMT Tri-Peg) 74098 (SMT Split Peg) 74105 (SMT No Peg) 70575 (Large Pocket Tri-Peg)

#### Vertical and Right Angle Series Combined

71164 (Vertical and Right Angle with Voided Circuits)

#### 2.2 PRODUCT SPECIFICATION TITLE AND DOCUMENT NUMBER

Single Row – Stackable Linear (SL) Connector System, PS-70400.

Assembly Connector SL Shrouded Header .100/2.54 Grid: Family Index, PS-70541.

REVISION:	ECR/ECN INFORMATION:	TITLE: Test Summary for SL Headers -				
Α	EC No: UCP2015-2459	Compariso	Comparison of Toller Compounders			
~	<u>DATE:</u> 2014 / 12 / 12	that Pro	<b>1</b> of <b>5</b>			
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:		
Т	S-70541-100	DMorgan	BBarker SMiller			
TEMPLATE FILENAME: TEST_SUMMARY[SIZE_A](V.2).DOC						

### **molex**<sup>®</sup> Test Summary

#### 3.0 QUALIFICATION

- 3.1 Compare resin properties from both compounders
- 3.2 Conduct molding trial runs with resin from new compounder
- 3.3 Compare molded housings dimensionally from both compounders
- 3.4 Produce final assemblies with molded housings from both compounders

3.5 Compare housing bow on connector assemblies before and after 260°C reflow process from both compounders

#### 4.0 DATA

4.1 Resin properties

Compounder (Toller)	Sample	Batch#	Ash content	melt viscosity @(Single Shear)@400 s/l(Pa-S)	Melting	Tensile Modulus, Mpa	Tensile Stress @ Break, Mpa	Tensile Strain @ Break, %	Flexural Modulus,Mpa	Flexural Stress, Mpa	DTUL @ 1.8 Mpa	Notched Charpy Impact, kJ/m2
Old	1	733280	33.7	242	286.8	11006	106.9	1.3	10638	155.1	244.7	6.4
Old	2	716692	34.4	201		annual skip						
Old	3	716690	34.1	218		annual skip						
Old	4	712130	33.4	201		annual skip						
Old	5	669459	33.6	215		annual skip						
Old	6	635740	34.6	183		11166	104.4	1.42	10851	151	241.0	6.11
New	1	724833	33.3	192	285.7	10828	111.2	1.5	10621	165	247.2	6.4
New	2	723050	33.8	210	285.0	11002	111.5	1.4	10741	162.9	247.0	6.3
New	3	723049	33	163	285.3	10897	112.9	1.4	10647	157.2	248.6	6.4
New	4	708334	35.2	286	285.6	11314	107.8	1.3	10787	159.4	250.5	5.9
New	5	697897	32.6	216	285.6	10727	113.8	1.5	10304	168.6	250.2	6.2
			ISO 3451	ISO 11433	ISO 11357	ISO 527	ISO 527	ISO 527	ISO 178	ISO 178	ISO 75	ISO 179/1eA

#### 4.2 Molding trial runs

A 25 circuit Tri-Peg housing was selected to evaluate. The evaluation consisted of a comparison of the following parameters:

Injection psi Screw Recovery Cool Time Cycle Time Part Weight Hold psi Hold Time Barrel Temperature


The Molding Process Engineer determined there was no difference between the resins produced by either toller compounder.

REVISION:	ECR/ECN INFORMATION:	TITLE: Test Summary for SL Headers - SHEET N					
•	EC No: UCP2015-2459		Comparison of Toller Compounders				
A	<u>DATE:</u> 2014/12/12	that Produce Housing Resins					
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:			
Т	S-70541-100	DMorgan	BBarker SMiller				
TEMPLATE FILENAME: TEST_SUMMARY[SIZE_A](V.2).DOC							

```
molex<sup>®</sup> TEST SUMMARY
```

4.3 Dimensional study from both compounders:

Dimensional checks were performed to insure there was no difference to parts produced with resin from both compounders. The dimensions selected for evaluation are the ones that have the most potential for being impacted by the compounder change, if there was a difference between the plastic resins.



4.4 Conducted trial assembly runs with housings run with resin from both compounders

Parts from both resin compounders were run through the assembly process with no issues. Attribute checks were performed on all samples. No defects were observed.


REVISION:	ECR/ECN INFORMATION:	TITLE: Test Summary for SL Headers - SHEET N							
A	EC No: UCP2015-2459	Compariso	<b>3</b> of <b>5</b>						
A	DATE: 2014 / 12 / 12	that Produce Housing Resins							
DOCUMENT NUMBER:		CREATED / REVISED BY:         CHECKED BY:         APPROVED BY:			/ED BY:				
Т	S-70541-100	DMorgan	BBarker	s SMiller					
TEMPLATE FILENAME: TEST_SUMMARY[SIZE_A](V.2).DOC									

# **molex**<sup>®</sup> TEST SUMMARY

4.5 Heat resistance on final assemblies from both compounders:

To ensure there were no issues with the assemblies reacting to heat, the parts were subjected to three (3) reflow passes per the profile shown below. The peak temperature was 260°C and peak time was 40 seconds.

Molex does not recommend exceeding 245°C.



# **molex**<sup>®</sup> Test Summary

#### 5.0 SUMMARY AND CONCLUSION:

The overall properties of the resin produced by both compounders are well within the manufacturers specifications.

There were no differences in the molding process with resin from either toller compounder.

The assembly process showed no differences using housings molded with resin from either toller compounder.

The dimensional checks were within specification and similar between both compounders

From the results of this evaluation Molex approves the use of resin from either toller compounder.

REVISION:	ECR/ECN INFORMATION:	TITLE: Test Summary for SL Headers -						
Α	EC No: UCP2015-2459	Compariso	<b>5</b> of <b>5</b>					
~	<u>DATE:</u> 2014 / 12 / 12	that Produce Housing Resins						
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:				
Т	S-70541-100	DMorgan	BBarker	SMiller				
	TEMPLATE FILENAME: TEST SUMMARY[SIZE A](V.2).DOC							

	1	0	9			8		7	6 5	4
			70067-077	78 TUBE I	PACAK	GING MA	TRIX		NOTES:	
F		TUBE LENGTH 22.05" - TUBE PAYLOAD LENGTH - 21.45"			1. STAPLES MAY BE USED TO SET UP					
ľ			LIES WITHOU				MBLIES WITH		CARTON ONLY. CARTON CLOSURES	
		PCB MC		S		PCB MO		S	MUST BE DONE WITH TAPES. 2. ORIENT ROD END PARALLELTO TUBE TO	
	CKT.	PARTS	PARTS	PARTS PER	CKT.	PARTS	PARTS	PARTS PER	MAXIMIZE TUBE QTYS IN BOX.	
	SIZE	PER TUBE	PER MAGAZINE	CARTON	SIZE	PER TUBE	PER MAGAZINE	CARTON	3. IF NECESSARY, ADD FOAM SHEET(S)	$\frown$
				(SPQ)				(SPQ)		(A)
E	2	72	216	3456	2	43	129	2064	4. PLACE ONE TUBE LABEL (85-15-0003) PER MAGAZINE TUBE LABEL TO CONTAIN	
	3	52	156	2496	3	35	105	1680	"PART NUMBER", "WORK ORDER,	
	4	42	126	2016	4	30	90	1440	:BOX NUMBER".	
	5	35	105	1680	5	26	78	1248		
	6 7	30 26	90 78	1440 1248	6 7	23 21	69 63	1104 1008		
	8	20	69	1240	8	19	57	912	-	Ľ
	0 9	23	63	1004		19	57	816	_	S
D	9 10	19	57	912	9 10	17	48	768	-	,
	10	19	51	816	11	15	40	708		
	12	16	48	768	12	14	43	672		
	13	15	45	720	13	13	39	624	ROD NUMBER TUBE NUMBER	
	13	14	43	672	14	13	36	576	70180-0182	$\langle \langle \rangle \rangle$
	15	13	39	624	15	11	33	528		
С	16	12	36	576	16	11	33	528		
	17 18	11 11	33	528 528	17 18	10 10	30 30	480 480		7.2
	10	10	30	480	10	9	27	480		— 1.Z
	20	10	30	480	20	9	27	432		
	21	9	27	432	21	8	24	384		
	22	9	27	432	22	8	24	384		
В	23	8	24	384	23	8	24	384		
	24	8	24	384	24	7	21	336		
	25	8	24	384	25	1	21	336		SYMBOLS THIS DRAWING CONTAINS INFORMATI DIMENSION UNITS SCALE CURI
										F = 0 GENERAL TOLERANCES (UNLESS SPECIFIED)
									DETAIL - 1	$\overline{\$} = 0 \qquad \text{ANGULAR TOL } \pm 0.5^{\circ} \qquad \text{EC N}$ $\overline{\$} = 0 \qquad 4 \text{ PLACES} \qquad \pm \qquad \text{DRV}$
										V = 0 3 PLACES ± APF
A										$\bigtriangledown$ = 02 PLACES $\pm$ INIT $\boxtimes$ = 01 PLACE $\pm$ DRV
										= 0 DRAFT WHERE APPLICABLE THIRD
	FORMAT: master-tb-pod REVISION: H DATE: 2018/01/18	NT STATUS	P1 RELEASE D 9	ATE 2019/05/	31 06:06:	39 <b>8</b>		7	6 5	WIST REMAIN WITHIN DIMENSIONS
	DATE: 2018/01/18	-	5			~		•	· · · ·	•

